


Flansa motor EAMF-A-44C-60G/H-S1

Numar piesa: 1460105

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Greutate produs	300 g
Codul interfetei motor In	60G 60H
Cod de interfata carcasa de cuplare	44C
Nota privind materialele	Conform RoHS