

## Prize de cuplare KD1-M3-A

Numar piesa: 151995

FESTO



## Fisa de date

| Caracteristica                                          | Valoare                                                             |
|---------------------------------------------------------|---------------------------------------------------------------------|
| Latimea nominala                                        | 1.5 mm                                                              |
| Presiune de functionare interval complet de temperatura | -0.095 MPa...1.2 MPa<br>-0.95 bar...12 bar<br>-13.775 psi...174 psi |
| Debit nominal standard (normalizat conform DIN 1343)    | 44 l/min                                                            |
| Debitul nominal standardizat conform ISO 8778           | 47.7 l/min                                                          |
| Mediu de operare                                        | Aer comprimat conform ISO 8573-1:2010 [7:-:-]                       |
| Nota referitoare la mediul de lucru/comanda             | Este posibila functionarea cu ulei                                  |
| Clasa de rezistenta la coroziune KBK                    | 1 - stres redus la coroziune                                        |
| Conformitatea LABS                                      | VDMA24364-B1/B2-L                                                   |
| Temperatura ambianta                                    | -10 °C...60 °C                                                      |
| Cuplu de strangere nominal                              | 0.6 Nm                                                              |
| Toleranta fata de cuplul de strangere nominal           | ± 10 %                                                              |
| Greutate produs                                         | 2.9 g                                                               |
| Conector pneumatic 1                                    | Filet exterior M3                                                   |
| Nota privind materialele                                | Conform RoHS                                                        |
| Material garnituri                                      | NBR                                                                 |
| Material arc                                            | otel inoxidabil aliaj inalt                                         |
| Material carcasa                                        | Alama, nichelata                                                    |
| Material garnitura de filet                             | NBR<br>Otel inoxidabil aliaj inalt                                  |
| Material piesa filetata                                 | Alama, nichelata                                                    |
| Material bila                                           | otel inoxidabil inalt aliat                                         |
| Material corp ventil                                    | Alama                                                               |
| Manson de deblocare a materialului                      | Alama, nichelata                                                    |