

Compensator de moment FKG-25-B

Numar piesa: 15234

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	25
Abatere radiala +/-	1 mm
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...120 °C
Sarcina maxim admisibila pe termen lung in directia fortei +/-	600 N
Greutate produs	511 g
Material compensator de moment	Aliaj de aluminiu forjat, anodizat Otel, galvanizat
Material furca	Otel galvanizat
Materialul piesei glisante	Alama