

Manometru MA-15-10-QS-6

Numar piesa: 153384

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 bar...10 bar
Dimensiune nominala, manometru	15
Structura constructiva	Manometru cu tub Bourdon fara unitate de masura
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	5
Tip de protectie	IP53
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	QS-6
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	Otel
Material vizor	PC
Culoarea carcasei	negru
Greutate produs	10 g
Scala	Scara unica bar (exterior)