

# Manometru MA-15-10-QS-8

Numar piesa: 153385

FESTO



## Fisa de date

| Caracteristica                              | Valoare                                            |
|---------------------------------------------|----------------------------------------------------|
| Interval de afisare                         | 0 bar...10 bar                                     |
| Dimensiune nominala, manometru              | 15                                                 |
| Structura constructiva                      | Manometru cu tub Bourdon fara unitate de masura    |
| Tipul de montare                            | Instalarea liniei                                  |
| Mediu de operare                            | Gaze inerte<br>lichide neutre                      |
| Nota referitoare la mediul de lucru/comanda | fara acetilena<br>fara oxigen                      |
| Presiune de lucru                           | 0 MPa...1 MPa<br>0 bar...10 bar<br>0 psi...145 psi |
| Factor de incarcare alternanta              | 0.66                                               |
| Clasa de precizie de masurare               | 5                                                  |
| Tip de protectie                            | IP53                                               |
| Temperatura medie                           | -20 °C...60 °C                                     |
| Temperatura ambianta                        | -20 °C...60 °C                                     |
| Conformitatea LABS                          | VDMA24364-B2-L                                     |
| Nota privind materialele                    | Conform RoHS                                       |
| Pozitie de conectare                        | Partea din spate, centrat                          |
| Conexiune pneumatica                        | QS-8                                               |
| Materiale care intra in contact cu mediul   | Alama                                              |
| Material pivot de insurubare                | Alama                                              |
| Material carcasa                            | Otel                                               |
| Material vizor                              | PC                                                 |
| Culoarea carcasei                           | negru                                              |
| Greutate produs                             | 10 g                                               |
| Scala                                       | Scara unica<br>bar (exterior)                      |