


## Flansa oscilanta SUA-20

Numar piesa: 157320

FESTO



### Fisa de date

| Caracteristica                       | Valoare                                      |
|--------------------------------------|----------------------------------------------|
| Dimensiune                           | 20                                           |
| Pozitie de instalare                 | orice                                        |
| Clasa de rezistenta la coroziune KBK | 2 - Solicitare moderata din cauza coroziunii |
| Conformitatea LABS                   | VDMA24364-B1/B2-L                            |
| Temperatura ambianta                 | -40 °C...90 °C                               |
| Greutate produs                      | 41 g                                         |
| Nota privind materialele             | Conform RoHS                                 |
| Material fixare                      | Aliaj de aluminiu forjat                     |
| Material bolt                        | Otel galvanizat                              |
| Material manson                      | Otel de arcuri                               |
| Material rulment                     | Material plastic                             |
| Material suruburi                    | Otel, galvanizat                             |
| Material siguranta                   | Otel de arcuri                               |
| Material arbore                      | Otel<br>cu capac de protectie                |