

Flansa oscilanta SUA-32

Numar piesa: 157322

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	32
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-40 °C...90 °C
Greutate produs	138 g
Nota privind materialele	Conform RoHS
Material fixare	Aliaj de aluminiu forjat
Material bolt	Otel galvanizat
Material manson	Otel de arcuri
Material rulment	Material plastic
Material suruburi	Otel, galvanizat
Material siguranta	Otel de arcuri
Material arbore	Otel cu capac de protectie