

Tester senzori SM-TEST-1

Numar piesa: 158481

FESTO



Fisa de date

Caracteristica	Valoare
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind CEM
Temperatura ambianta	0 °C...40 °C
Domeniu de tensiune de lucru CC	12 V...20 V
Alimentare cu tensiune	Doua baterii de 9V
Afisaj gata de functionare	LED verde
Tip de protectie	IP20
Conformitatea LABS	VDMA24364-B2-L