

Purja condens WA-1-B

Numar piesa: 158497

FESTO



Fisa de date

Caracteristica	Valoare
Tip de actionare	mecanic
Pozitie de instalare	vertical +/- 10°
Actionare manuala	cu palpare
Purjare a condensului	complet automat
Structura constructiva	mecanica externa complet automata
Variabila masurata	Nivel de umplere
Functie de ventil	2/2 monostabil inchis
Presiune de lucru	4 bar...16 bar
Mediu de operare	Apa
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-20 °C...60 °C
Temperatura medie	0 °C...60 °C
Temperatura ambianta	0 °C...60 °C
Greutate produs	210 g
Tipul de montare	Instalarea liniei
Conexiune conducta de condens	G1/4
Conexiune pneumatica	M9
Material carcasa	Alama PA