

Manometru cu flansa FMA-50-2,5-1/4-EN

Numar piesa: 159598

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 bar...2.5 bar
Intervalul de afisare	0 psi...36.25 psi
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	50
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea panoului frontal
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...0.25 MPa 0 bar...2.5 bar 0 psi...36.25 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	2,5
Tip de protectie	IP43
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	G1/4
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	ABS
Material vizor	SAN
Material inel de fixare	Otel

Caracteristica	Valoare
Culoarea carcasei	negru
Greutate produs	100 g
Scala	Scara dubla bar (exterior) psi (intern)