

Rezervor de aer comprimat|Vas sub presiune CRVZS-0.1

Numar piesa: 160233

FESTO



Fisa de date

Caracteristica	Valoare
Volum	0,1 l
Pozitie de instalare	orice
Conform cu standardul	AD 2000
Presiune de lucru	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.78 psi...232 psi
Autorizare	CRN TÜV
Organizatia emitenta a certificatului	TSSCARN0H17477.5C
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [-:~::~-] Azot
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura medie	-10 °C...100 °C
Temperatura ambianta	-10 °C...100 °C
Cuplu de strangere max. filet de conectare	15 Nm
Greutate produs	226 g
Tipul de montare	Cleme de sustinere
Conexiune pneumatica	G1/8
Nota privind materialele	Conform RoHS
Material rezervor de aer comprimat	Otel inoxidabil aliaj inalt
Material cleme de sustinere	otel inoxidabil inalt aliat