


Pozitii multiple- SET DPVU-40

Numar piesa: 161198

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Greutate produs	155 g
Nota privind materialele	Conform RoHS
Material flansa	Aliaj de aluminiu forjat
Material suruburi	Otel galvanizat
Material stift cilindric	Otel galvanizat