

Flansa oscilanta SZF-25

Numar piesa: 161820

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	25
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-40 °C...90 °C
Greutate produs	30 g
Nota privind materialele	Conform RoHS
Material fixare	otel inoxidabil aliaj inalt
Material rulment	Material plastic
Material suruburi	Otel, galvanizat