

# Amortizor de zgomot UC-QS-6H

Numar piesa: 165007

FESTO



## Fisa de date

| Caracteristica                              | Valoare                                       |
|---------------------------------------------|-----------------------------------------------|
| Pozitie de instalare                        | orice                                         |
| Unitate de ambalare                         | 1                                             |
| Presiune de lucru                           | 0 MPa...1 MPa<br>0 bar...10 bar               |
| Debit in raport cu atmosfera                | 800 l/min                                     |
| Mediu de operare                            | Aer comprimat conform ISO 8573-1:2010 [7:-:-] |
| Nota referitoare la mediul de lucru/comanda | Este posibila functionarea cu ulei            |
| Conformitatea LABS                          | VDMA24364-B1/B2-L                             |
| Nivel de presiune acustica                  | 60 dB(A)                                      |
| Temperatura ambianta                        | -10 °C...70 °C                                |
| Greutate produs                             | 1.1 g                                         |
| Conexiune pneumatica                        | QS-6                                          |
| Material insertie amortizor de zgomot       | PE                                            |
| Material pivot de insurubare                | PE                                            |
| Nota privind materialele                    | Conform RoHS                                  |