

Fibra optica
SOEZ-LLG-SE-0,5-M4
Numar piesa: 165357

FESTO



Fisa de date

Caracteristica	Valoare
Metoda de masurare	Senzor cu fascicul transversal Fibra optica
Temperatura ambianta	-20 °C...160 °C
Dimensiune	M4
Greutate produs	46 g
Material carcasa	Alama cromat
Limita superioara a intervalului de reglare	280 mm
Temperatura ambientala de instalare in miscare	-20 °C...120 °C
Tip de protectie	IP54
Conformitatea LABS	VDMA24364-B2-L