

Bobina
MSN1W-24AC/12DC
Numar piesa: 170152

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Ora min. de preluare	10 ms
Ciclu de lucru	100%
Factorul de putere cos {phi}	0.7
Caracteristici bobina	12 V CC: 5,0 W 24 V CA: 50 Hz, putere de preluare 7,5 VA, putere de mentinere 5,0 VA 24 V CA: 60 Hz, putere de preluare 5,0 VA, putere de mentinere 3,7 VA
Fluctuatii de tensiune admise	la 50Hz ±10 % la 60Hz -10...+20 %
Conformitatea LABS	VDMA24364-C1-L
Temperatura medie	-10 °C...50 °C
Tip de protectie	IP65
Temperatura ambianta	-10 °C...50 °C
Greutate produs	80 g
Conector electric	3 pini Forma A clipbar conform DIN EN 175301-803
Tipul de montare	prinsa cu clema cu clema de retinere
Material carcasa	PA
Material contacte de cuplare	Otel
Material infasurare	Cupru