

**Priza
MSSD-C-4P**
Numar piesa: 171157

FESTO



Fisa de date

Caracteristica	Valoare
Tipul de montare	pe ventil electromagnetic cu surub central M3
Pozitie de instalare	orice
Greutate produs	22 g
Conector electric	3 pini Priza inclinata Forma A conform DIN EN 175301-803 design patrat MSC Versiune patrata MSN1
Presetupa	Pg9
Diametrul cablului	6 mm...8 mm
Sectiunea transversala nominala a conductorului	1.5 mm ²
Tip de protectie	IP65
Temperatura ambianta	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Material carcasa	Material plastic
Culoarea carcasei	negru