

Adaptor T FB-TA-M12-5POL

Numar piesa: 171175

FESTO



Fisa de date

Caracteristica	Valoare
Tipul de montare	cu orificiu de trecere
Greutate produs	59 g
Conector electric	5 pini M12x1 / M12x1 stecher / prize
Domeniu de tensiune de lucru CC	10 V...30 V
Capacitate de transport al curentului	4 A
Tip de protectie	IP67
Temperatura ambianta	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L