


Unitate ghidare EAGF-V2-KF-80-320

Numar piesa: 1725848

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	80
Cursa	320 mm
Reactie de recul	0 µm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Clasa de rezistenta la coroziune KBK	0 - nu este afectat de coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	2300 N
Forta max. Fy statica	3120 N
Forta max. Fz	2300 N
Forta max. Fz statica	3120 N
Moment max. Mx	170 Nm
Moment max. Mx static	231 Nm
Max. Moment My	191 Nm
Moment My static max.	259 Nm
Moment max. Mz	191 Nm
Moment Mz static max.	259 Nm
Forta de deplasare	40 N
Masa in miscare	7606 g
Greutate produs	12949 g
Centrul de greutate al masei in miscare la o cursa de 0 mm	54 mm
Centrul de greutate suplimentar al masei in miscare la o cursa de 10 mm	3.8 mm
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat anodizat
Material placa de jug	Otel