


Set axial EAMM-A-P5-28B-28A

Numar piesa: 1731474

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	12 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	0.28 kgmm ²
Cuplu transmisibil	1.1 Nm
Greutate produs	40 g
Cod de interfata actuator	P5-28B
Codul interfetei motor In	28A
Cod de interfata carcasa de cuplare	28B
Nota privind materialele	Conform RoHS