

Ventuză vacuum VAS-2-M3-NBR

Numar piesa: 173438

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	1 mm
Diametrul ventuzei	2 mm
Diametru de aspiratie eficient	1.6 mm
Pozitie de conectare	sus
Forma de ventuza	rotund plat
Presiune de lucru	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi
Presiunea nominala de functionare	-0.07 MPa -0.7 bar -10.15 psi
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-20 °C...80 °C
Fora de smulgere la 70 % vacuum	0.14 N
Fora de mentinere la presiune de lucru nominala	0.14 N
Filet de fixare	M3
Fixarea ventuzei	M3
Racord de vacuum	M3
Culoare	negru
Duritate Shore	55 +/- 5
Material pivot de insurubare	otel inalt aliat
Nota privind materialele	Conform RoHS
Material ventuze	NBR