


Combinatie filtre fine LFMBA-3/8-D-MIDI-NPT

Numar piesa: 173746

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Midi
Seria	D
Pozitie de instalare	vertical
Finete de filtrare	0.01 µm
Eficienta filtru	99.9999 %
Purjare a condensului	palpare manuala
Protectie pahar	Cos metalic de protectie
Presiune de lucru	1 bar...16 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [6:8:4] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [1:7:2] Gaze inerte
Temperatura medie	1.5 °C...60 °C
Continut de ulei rezidual	0.01 mg/m³
Temperatura ambianta	-10 °C...60 °C
Tipul de montare	Instalarea liniei cu accesorii
Conector pneumatic 1	3/8 NPT
Conexiune pneumatica 2	3/8 NPT
Nota privind materialele	Conform RoHS
Material filtru	Fibra de borosilicat
Material carcasa	Zinc turnat sub presiune PC