

Modul ramificare FRM-3/8-D-MIDI-NPT

Numar piesa: 173927

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Structura constructiva	Modul de ramificare
Presiune de lucru	0 MPa...1.6 MPa 0 bar...16 bar
Diametru nominal normal pe directia principala de curgere 1->2	6700 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Gaze inerte
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura de depozitare	-10 °C...60 °C
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Gaze inerte
Temperatura medie	-10 °C...60 °C
Temperatura ambianta	-10 °C...60 °C
Greutate produs	522 g
Conector pneumatic 1	3/8 NPT
Conexiune pneumatica 2	3/8 NPT
Conector pneumatic 3	G1/2
Conexiune pneumatica 4	G1/4
Nota privind materialele	Conform RoHS
Material carcasa	Aluminiu turnat sub presiune