

Modul ramificare FRM-H-1/4-D-MINI-NPT

Numar piesa: 173933

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Structura constructiva	Modul de ramificare
Presiune de lucru	0.015 MPa...1.6 MPa 0.15 bar...16 bar
Diametru nominal normal pe directia principala de curgere 1->2	2000 l/min
Medii de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Gaze inerte
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura de depozitare	-10 °C...60 °C
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [7:-:-] Gaze inerte
Temperatura medie	-10 °C...60 °C
Temperatura ambianta	-10 °C...60 °C
Greutate produs	198 g
Conector pneumatic 1	1/4 NPT
Conexiune pneumatica 2	1/4 NPT
Conector pneumatic 3	G1/4
Conexiune pneumatica 4	G1/4
Nota privind materialele	Conform RoHS
Material carcasa	Aluminiu turnat sub presiune