

Talpa fixare HNC-50

Numar piesa: 174371

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	50
Conform cu standardul	ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Greutate produs	353 g
Nota privind materialele	Conform RoHS
Material fixare	Otel galvanizat
Material suruburi	Otel galvanizat