

Fus oscilant ZNCF-40

Numar piesa: 174412

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Pe baza standardului	ISO 15552
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Greutate produs	285 g
Nota privind materialele	Conform RoHS
Material fixare	Otel inoxidabil turnat
Material suruburi	Otel galvanizat