

Fus oscilant ZNCF-125

Numar piesa: 174417

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	125
Pe baza standardului	ISO 15552
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Greutate produs	3484 g
Nota privind materialele	Conform RoHS
Material fixare	Otel inoxidabil turnat
Material suruburi	Otel galvanizat