

Cuplaj
EAMC-65-90-25-32
Numar piesa: 1745817

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	25 mm
Diametru de montare 2	32 mm
Dimensiune	65
Lungime nominala	90 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	417 kgmm ²
Cuplu transmisibil	92 Nm
Greutate produs	535 g
Nota privind materialele	Conform RoHS