

**Cuplaj**  
**EAMC-40-66-XX-20**

Numar piesa: 176037

**FESTO**



**Fisa de date**

| Caracteristica               | Valoare                |
|------------------------------|------------------------|
| Diametru de montare 2        | 20 mm                  |
| Dimensiune                   | 40                     |
| Lungime nominala             | 66 mm                  |
| Pozitie de instalare         | orice                  |
| Turatie max.                 | 6500 1/min             |
| Conformitatea LABS           | VDMA24364-B2-L         |
| Temperatura de depozitare    | -25 °C...60 °C         |
| Umiditate relativa           | 0 - 95 %               |
| Temperatura ambianta         | -25 °C...60 °C         |
| Momentul de inertie al masei | 42.3 kgmm <sup>2</sup> |
| Greutate produs              | 139 g                  |
| Nota privind materialele     | Conform RoHS           |