

Flansa oscilanta SUA-80-R3

Numar piesa: 176890

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	80
Pozitie de instalare	orice
Variante	Protectie anticoroziune ridicata
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Greutate produs	772 g
Nota privind materialele	Conform RoHS
Material fixare	Aliaj de aluminiu forjat cu capac de protectie
Material bolt	otel inoxidabil aliaj inalt
Material manson	Otel de arcuri
Material rulment	Material plastic
Material suruburi	otel inoxidabil inalt aliat
Material siguranta	otel inoxidabil aliaj inalt
Material arbore	otel inoxidabil inalt aliat