

Distribuitoare multipin MPV-E/A12-M8

Numar piesa: 177670

FESTO



Fisa de date

Caracteristica	Valoare
Tipul de montare	optional: cu orificiu de trecere cu sina omega
Greutate produs	120 g
Tehnologie de conectare electrica I/O	M8 3 pini
Domeniu de tensiune de lucru CC	10 V...30 V
Capacitate de transport curent per slot	1 A
Capacitate de transport al curentului	4 A
Tip de protectie	IP65 in stare asamblata conform IEC 60529
Temperatura ambianta	-20 °C...80 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	ranforsat cu PA6
Material priza	Alama