

# Teava plastic PQ-PA-18X2X3000

Numar piesa: 177730

FESTO



## Fisa de date

Caracteristica	Valoare
Ø exterior	18 mm
Ø interior	14 mm
Presiune de lucru in functie de temperatura	-0.95 bar...15 bar
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-25 °C...75 °C
Temperatura ambianta	-25 °C...75 °C
Greutatea produsului in functie de lungime	0.103 kg/m
Culoare	negru
Material furtun	PA