

Teava
PQ-AL-22X1X3000
Numar piesa: 177735

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	22 mm
Ø interior	20 mm
Presiune de lucru in functie de temperatura	-0.95 bar...15 bar
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-25 °C...75 °C
Temperatura ambianta	-30 °C...75 °C
Greutatea produsului in functie de lungime	0.178 kg/m
Culoare	argintiu
Nota privind materialele	Conform RoHS
Material furtun	Aliaj de aluminiu forjat