


Cuplaj
EAMD-42-40-20-16X25-U
Numar piesa: 1781043

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	20 mm
Diametru de montare 2	16 mm
Dimensiune	42
Lungime nominala	40 mm
Pozitie de instalare	orice
Turatie max.	6000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	39 kgmm ²
Cuplu transmisibil	21 Nm
Greutate produs	189 g
Nota privind materialele	Conform RoHS