

Manometru MA-23-10-R1/8

Numar piesa: 183897

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 bar...10 bar
Intervalul de afisare	0 psi...145 psi
Dimensiune nominala, manometru	23
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Factor de incarcare alternanta	0.6
Clasa de precizie de masurare	4
Tip de protectie	IP44
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	R1/8
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	Alama
Material vizor	PC
Culoarea carcasei	negru
Greutate produs	27 g
Scala	Scala dubla bar (exterior) psi (intern)