


Ventil de panou SV/O-3-PK-3X2

Numar piesa: 184135

FESTO



Fisa de date

Caracteristica	Valoare
Functie de ventil	2x3/2 normal inchis monostabil
Debit nominal standard (normalizat conform DIN 1343)	70 l/min
Racord pneumatic de lucru	PK-3
Presiune de lucru	0 bar...8 bar
Tip de revenire	arc mecanic
Latimea nominala	2.5 mm
Principiul de etansare	slab
Pozitie de instalare	orice
Tipul de comanda	direct
Directia de curgere	nu este reversibil
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	34 g
Tipul de montare	cu orificiu de trecere
Conector pneumatic 1	PK-3
Conexiune pneumatica 2	PK-3
Material garnituri	NBR