

Mecanism unisens FLSM-6-L

Numar piesa: 188523

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	6
Directia de rotire	Rotatie la stanga
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	0 °C...60 °C
Cuplu teoretic la 0,6 MPa (6 bari, 87 psi)	0.15 Nm
Greutate produs	100 g
Material carcasa	Aliaj de aluminiu forjat
Material manson	Otel
Material arbore	Otel