

Tub plastic PUN-CM-4-SW

Numar piesa: 188882

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	4 mm
raza de indoire relevanta pentru debit	17 mm
Ø interior	2.5 mm
Raza min. de indoire	8 mm
Proprietati ale furtunului	lant energetic adecvat
Presiune de lucru in functie de temperatura	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Rezistenta la suprafata	0.01 MOhm...10 MOhm
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-35 °C...60 °C
Greutatea produsului in functie de lungime	0.00993 kg/m
Conexiune pneumatica	pentru racordul push-in cu Ø exterior de 4 mm
Culoare	negru
Duritate Shore	D 52 +/-3
Nota privind materialele	Conform RoHS
Material furtun	TPE-U (PU)