

Gripper vacuum ESG-8

Numar piesa: 189170

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul ventuzei	8 mm
Pozitie de instalare	vertical
Caracteristici speciale	antistatic
Structura constructiva	Racord de vid, sus Racord de vacuum lateral cu compensarea inaltimii cu compensare lunga a inaltimii
Atribuirea suportului de ventuza	Dimensiune 2
Forma de ventuza	rotund plat
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Temperatura ambianta	-30 °C...200 °C
Racord de vacuum	M5 M10x1 QS-6 PK-4
Nota privind materialele	Conform RoHS
Material ventuze	BR FPM NBR PUR VMQ (silicon)