

Gripper vacuum ESG-20X60

Numar piesa: 189190

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea ventuzei	20x60 mm
Pozitie de instalare	vertical
Structura constructiva	Racord de vid, sus Racord de vacuum lateral cu compensarea inaltimii cu compensare lunga a inaltimii
Atribuirea suportului de ventuza	Dimensiune 5
Forma de ventuza	oval plat
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7::-:]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Temperatura ambianta	-10 °C...70 °C
Racord de vacuum	G1/8 G1/4
Nota privind materialele	Conform RoHS
Material ventuze	NBR