

Suport ventuza vacuum ESH-HA-3-QS

Numar piesa: 189197

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	5 mm
Volum	0.52 cm ³
Pozitie de instalare	orice
Structura constructiva	Racord de vid, sus
Atribuirea suportului de ventuza	Dimensiune 3
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	0 °C...60 °C
Greutate produs	20 g
Tipul de montare	cu piulita de blocare
Fixarea ventuzei	M4
Racord de vacuum	QS-6
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt