

Suport ventuza vacuum ESH-HB-1-PK

Numar piesa: 189204

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	2.5 mm
Volum	0.108 cm ³
Pozitie de instalare	orice
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 1
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	4 g
Tipul de montare	cu filet interior
Fixarea ventuzei	Diametru 3 mm
Racord de vacuum	PK-3
Nota privind materialele	Conform RoHS
Material garnituri	NBR Otel
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt