

# Suport ventuza vacuum ESH-HB-2-QS

Numar piesa: 189205

FESTO



## Fisa de date

Caracteristica	Valoare
Latimea nominala	2 mm
Volum	0.418 cm <sup>3</sup>
Pozitie de instalare	orice
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 2
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	0 °C...60 °C
Greutate produs	13 g
Tipul de montare	cu filet interior
Fixarea ventuzei	Diametru 4 mm
Racord de vacuum	QS-6
Nota privind materialele	Conform RoHS
Material garnituri	NBR Otel
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt