

Suport ventuza vacuum ESH-HB-4-PK

Numar piesa: 189210

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	2.5 mm
Volum	0.416 cm ³
Pozitie de instalare	orice
Structura constructiva	Racord de vacuum lateral
Atribuirea suportului de ventuza	Dimensiune 4
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	25 g
Tipul de montare	cu filet interior
Fixarea ventuzei	M6
Racord de vacuum	PK-4
Nota privind materialele	Conform RoHS
Material garnituri	NBR Otel
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt