

Suport ventuza vacuum ESH-HD-1-QS

Numar piesa: 189233

FESTO



Fisa de date

Caracteristica	Valoare
Compensarea inaltimii suport de ventuza	3 mm
Latimea nominala	3 mm
Volum	0.241 cm ³
Pozitie de instalare	vertical
Structura constructiva	Racord de vacuum lateral cu compensarea inaltimii
Atribuirea suportului de ventuza	Dimensiune 1
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7::-]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	0 °C...60 °C
Greutate produs	13 g
Tipul de montare	cu piulita de blocare
Fixarea ventuzei	Diametru 3 mm
Racord de vacuum	QS-4
Nota privind materialele	Conform RoHS
Material garnituri	NBR Otel
Suport material	Aluminiu Alama, nichelata POM Otel calit Otel aliaj inalt