

Mecanism unisens FLSR-40-L

Numar piesa: 19037

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Directia de rotire	Rotatie la stanga
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu teoretic la 0,6 MPa (6 bari, 87 psi)	20.03 Nm
Greutate produs	1820 g
Material carcasa	Aluminiu turnat
Material manson	Otel calit
Material arbore	Otel de calire