

Manometru PAGL-HP3-63-60-G14-RC

Numar piesa: 1908519

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 bar...60 bar 0 MPa...6 MPa
Intervalul de afisare	0 psi...870 psi
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	63
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...6 MPa 0 bar...60 bar 0 psi...870 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	1,6
Tip de protectie	IP65
Temperatura de depozitare	-40 °C...70 °C
Temperatura medie	0 °C...60 °C
Temperatura ambianta	0 °C...60 °C
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Radial dedesubt
Conexiune pneumatica	G1/4
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	Otel

Caracteristica	Valoare
Material vizor	PS
Culoarea carcasei	argint
Greutate produs	80 g
Scala	Scala tripla MPa (exterior) bar (exterior) psi (intern)