

Ventuză vacuum fara conector ESV-40-SNA

Numar piesa: 190993

FESTO



Fisa de date

Caracteristica	Valoare
Raza min. a piesei de prelucrat	230 mm
Diametrul ventuzei	40 mm
Volum de aspiratie	1.566 cm ³
Pozitie de conectare	sus
Pozitie de instalare	orice
Caracteristici speciale	antistatic
Forma de ventuza	rotund plat
Presiune de lucru	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Presiunea nominala de functionare	-70 kPa -0.7 bar -10.15 psi
Rezistenta la suprafata	200 Ohm
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-A1-L
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-10 °C...70 °C
Fora de mentinere la presiune de lucru nominala	69.6 N
Greutate produs	7.4 g
Culoare	punct alb/negru
Duritate Shore	50 +/- 5
Nota privind materialele	Conform RoHS
Material ventuze	NBR