


## Ventuză vacuum fara conector ESV-150-SU

Numar piesa: 191012

FESTO



### Fisa de date

| Caracteristica                                  | Valoare                                                     |
|-------------------------------------------------|-------------------------------------------------------------|
| Raza min. a piesei de prelucrat                 | 480 mm                                                      |
| Diametrul ventuzei                              | 150 mm                                                      |
| Volum de aspiratie                              | 173.826 cm <sup>3</sup>                                     |
| Pozitie de conectare                            | sus                                                         |
| Pozitie de instalare                            | orice                                                       |
| Forma de ventuza                                | rotund plat                                                 |
| Presiune de lucru                               | -95 kPa...0 kPa<br>-0.95 bar...0 bar<br>-13.775 psi...0 psi |
| Presiunea nominala de functionare               | -70 kPa<br>-0.7 bar<br>-10.15 psi                           |
| Mediu de operare                                | aer atmosferic conform ISO 8573-1:2010 [7:::]               |
| Conformitatea LABS                              | VDMA24364 zona III                                          |
| Siguranta alimentara                            | vedeti informatii detaliate despre material                 |
| Temperatura ambianta                            | -20 °C...60 °C                                              |
| Fora de mentinere la presiune de lucru nominala | 900 N                                                       |
| Greutate produs                                 | 361 g                                                       |
| Culoare                                         | albastru                                                    |
| Duritate Shore                                  | 60 +/- 5                                                    |
| Nota privind materialele                        | Conform RoHS                                                |
| Material ventuze                                | PUR                                                         |