


Amortizor de soc YSRW-7-10

Numar piesa: 191193

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	7
Cursa	10 mm
Amortizare	autoreglare caracteristica slaba
Pozitie de instalare	orice
Detectarea pozitiei	fara
Viteza max. de impact	3 m/s
Timp de resetare la temperatura camerei	0.2 s
Timp de resetare la temperatura ambientala minima	1 s
Mod de functionare	cu apasare cu simpla actiune
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...80 °C
Lungime de amortizare	10 mm
Forta max. de ridicare	300 N
Consumul max. de energie pe cursa	2.5 J
Consum max. de energie pe ora	15000 J
Energie reziduala max.	0.01 J
Forta de restabilire	1.2 N
Forta minima de insertie	10 N
Greutate produs	18 g
Interval de masa	5 kg
Tipul de montare	cu piulita de blocare
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material carcasa	Otel aliaj inalt
Material tija de piston	otel aliaj inalt